

# BAJAJ LAB GIN SR 500

### USER MANUAL AND TECHNICAL BULLETIN

**66**Quality is never an accident. It is the result of an intelligent effort. There must be a will to produce a superior thing.

- JOHN RUSKIN

## DESIGNED WITH THE USER IN MIND; OVER 60 YEARS OF EXPERIENCE AT HAND!




Manufactured in Technical Collaboration With Central Institute for Research on Cotton Technology (CIRCOT), ICAR, Govt. of India.

# BAJAJ LAB GIN SR 500

#### **Salient Features :**

Production Capacity 48 to 50 Seed Cotton Samples of 250 gms. per hour Power Required : 2 HP 3 Phase Electric Motor Roller Length 500 mm

> Designed a Developed to gin large quantity of seed cotton samples quickly to test their fibre a. seed quality. Highly suitable for use by cotton breeders, traders a also by Ginners for their own out turn Evaluation.



Double Roller Cotton Gin~Auto Feeder~Pre Cleaner~Lint Cleaner~Seed Cotton Opener & Cleaner~Pneumatic Conveying and Distribution System of Unginned Cotton for Automatic Plants~Belt Conveyors & Pneumatic Conveying System for Cotton Lint~Cottonseed Conveyors, Elevators~Electricals and

### **ALWAYS USE**

BAJAJ GENUINE SPARE PARTS FOR HIGHER QUALITY OUTPUT & BETTER LIFE OF MACHINE

Note : Features shown do not necessarily show the machine / equipments in it's standards form. In view of our policy of continuously improving our products, we reserve the right to alter specifications or designs without prior notice & without liability .



### BAJAJ CONEAGLE LLC

1900 Market St., Millbrook, AL 36054. USA Telephone: (334) 517-6139/40/41 Fax: (334) 571-6142 email: sales@bajajconeagle.com website: www.bajajconeagle.com

